

**\* SEE TEMPLATE ON BACK \***  
Refer to Dimensions Shown to Ensure Accuracy

**GENEVA**  
Wall Mount Hinge – Short Back Plate  
CAT. NO. GEN074

**\*NOTE:** Do not exceed either maximum weight or width when choosing proper quantity of hinges.

**Important Information:**

1) The Cat. No. GEN074 Short Back Plate Geneva Wall Mount Hinge offers two different templates. The Regular Clearance Template allows 1/8" (3mm) to 1/4" (6mm) clearance. The Tight Clearance Template allows for a tighter clearance of 1/32" (1mm) to 5/32" (4mm), and is commonly used on installations where vinyl seals are not being used.

2) This hinge contains a dual degree pivot pin. The pivot pin is set for normal door closing position. You have the option of altering the closing position of the door 5 degrees inward by utilizing the opposite side of the pivot pin, which has been pre-machined (see Section 3 of Cat. No. SDT22 Frameless Shower Door Guide for this procedure). Special order custom pivot pins are available (Cat.No. GENPIN) that can be machined at any angle up to 45 degrees

**Specifications:**

|                 |  |
|-----------------|--|
| Glass Sizes:    | 3/8" (10mm) to 1/2" (12mm) thick tempered safety glass |
| Construction:   | Solid brass  |
| Closing Type:   | Self-centering when within 15° of closed position      |
| Cutout Required |  |
| Includes:       | Gaskets, screws and template                           |

**Maximum Door Capacities for Two Hinges or Three Hinges**

|                      |                |                 |
|----------------------|----------------|-----------------|
| Maximum Door Weight: | 80 lbs.(36 kg) | 120 lbs.(54 kg) |
| Maximum Door Width:  | 28"(711mm)     | 32"(813mm)      |

**Use of Gaskets:**

For 3/8" (10mm) Glass: Use one thick gasket on each side  
For 1/2" (12mm) Glass: Use one thin gasket on each side



**Recommendations:**

For public safety, we recommend the use of only tempered safety glass. Do not use power tools when installing these hinges.

**Maintenance Guidelines:**

- Our hinges are greased at the factory for quiet and trouble-free operation. If there is any squeaking that occurs after installation, put a drop of "3 in 1 Oil" (also known as "household oil") on the white nylon washer that the hinge body pivots on. This washer is the component that acts as a buffer, so the body of the hinge doesn't pivot directly on the brass center block. This solution doesn't require the disassembly of the hinge. **Note: Do not use spray lubricant on these hinges.** If the hinge has been disassembled, upon re-assembly, use white lithium grease to lubricate the interior mechanism.
- Never use an abrasive cleaner on the hardware. Many of the components are coated with a clear lacquer that will be irreparably damaged if subjected to harsh, abrasive chemicals. Advise your customer that drying the hardware with a clean, soft towel on a daily basis is the best way to maintain the hardware. If mineral deposits build-up, mix a couple of drops of a mild liquid soap (such as Ivory or a similar product) into a cup of warm water. Using a soft, non-abrasive cloth, clean the hardware. Rinse thoroughly with clean, warm water and dry.

**IMPORTANT:** Project measurements from the edge of the glass.



 ALWAYS USE DIMENSIONS TO ENSURE ACCURACY

**GENEVA**  
Wall Mount Hinge – Short Back Plate  
CAT. NO. GEN074