




SENIOR PRIMA

Top or Bottom Mount Hinge

CAT. NO. SRPPH01

***NOTE:** Do not exceed either maximum weight or width when choosing proper hinges.

Important Information:

Template Options: The Top or Bottom Mount SRPPH01 Hinge offers two choices of templates. Refer to the lower left hand corner of this page for the selections. The Edge Mount Template has a full leg cutout that allows a full length vertical seal on the hinge side.

The Inset Mount Template enables the door to avoid hitting a towel bar, or some other protrusion from the wall.

Optional Pivot Pins: Optional 5° Pivot Pins (Cat. No. SRPIVP1N) are sold as a set, one pin for the top hinge and one pin for the bottom hinge. These 5° offset Pivot Pins allow the installer to adjust the closing position of the door 5° inwards or outwards.

Specifications:

Glass Sizes:	1/2"(12mm) thick tempered safety glass
Construction:	Solid brass
Closing Type:	Self-centering when within 15° of closed position
Cutout Required	
Includes:	Gaskets, screws and template

Max Clamping Screw Torque: 60-70 lbf-in (677.99.790.9 cN-m)

Maximum Door Capacities for Two Hinges

Maximum Door Weight: 145 lbs.(66 kg)

Maximum Door Width: 36"(914mm)

Use of Gaskets:

For 1/2" Glass: Use one thin gasket on one side and one thick gasket on the other side
For 12mm Glass: Use one thick gasket on both sides

Recommendations:




For public safety, we recommend the use of only tempered safety glass. Do not use power tools when installing these hinges.

Maintenance Guidelines:

- Never use an abrasive cleaner on the hardware. Many of the components are coated with a clear lacquer that will be irreparably damaged if subjected to harsh, abrasive chemicals. Advise your customer that drying the hardware with a clean, soft towel on a daily basis is the best way to maintain the hardware. If mineral deposits build-up, mix a couple of drops of a mild liquid soap (such as Ivory or a similar product) into a cup of warm water. Using a soft, non-abrasive cloth, clean the hardware. Rinse thoroughly with clean, warm water and dry.



IMPORTANT: Project measurements from the edge of the glass.



SENIOR PRIMA


Top or Bottom Mount Hinge

CAT. NO. SRPPH01

Edge Mount Method ($9/16"$ (14mm) Clearance)

For Technical Assistance in the United States and Canada 1.800.421.6144. Press 2, then option 1

C.R. Laurence Co., Inc. • 2503 E. Vernon Ave., Los Angeles, CA 90058 • 1.800.421.6144 • crlaurence.com



Inset Mount Method (9/16" (14mm) Clearance)

© Copyright 2025, C.R. Laurence Co., Inc_SDT22_25